## **Agitation & Mixing Overview Datasheet**

The information listed on this document gives an overview of the 2 different types of agitation technology SR-TEK can offer and how it integrates with our products. The information listed below can assist you with choosing the most suitable agitation technology and mixing element design for your application and requirements. If you are unsure or require a specific study for your application, please contact us direct and we will be happy to assist.

r extreme operating oheres. Resistant to high aless-steel. L tanks. long lasting, no overload o control at low speed, table speed th high viscosity fluids
nless-steel. L tanks. long lasting, no overload o control at low speed, table speed th high viscosity fluids
L tanks. long lasting, no overload control at low speed, table speed th high viscosity fluids
long lasting, no overload control at low speed, table speed th high viscosity fluids
o control at low speed, table speed th high viscosity fluids
o control at low speed, table speed th high viscosity fluids
table speed th high viscosity fluids
th high viscosity fluids
th high viscosity fluids
r applications were
i programmable mixing.
eversible, good for low
·····, g······
res, require time to learn
<i>i</i> 1
PLC interface,
e.
s with low to medium
o available on request.
ity, ease of maintenance s with no exothermic om speed is no issue.
stir throughout the thixotropic fluids. vide homogeneity.
ly suited for low viscosity tain, the round paddles nogeny mix throughout
ording to the design of essel filled with water.
Anchor Blade
de de de de de de de de de de de de de d

**SR-TEK**